

TRADE SIZE	CATALOG NUMBER	HUB TYPE	WIRE SIZE (AWG, MCM)													
			6	4	3	2	1	1/0	2/0	3/0	4/0	250	300	350	400	500
4" (-0)	OLB-0M*, LB108, MOUB-0, MOT-0, MOLBD-0, MOC-0, MOLB-0	All		58	49	41	31	26	21	18	15	12	10	9	8	3
	OLB-0	All		58	49	41	31	26	21	18	15	12	10	9	3	
	OC-0M*, OLR-0, OLL-0, OT-0M*	All		58	49	41	31	26	21	18	15	12	10	3		
	OC-0, LB107	All		58	49	41	31	26	21	18	15	12	3			
	OR-0, LL107, LR107	All		58	49	41	31	26	21	18	15	3				
	T107, C107	All		58	49	41	31	26	21	3						
3-1/2" (-9)	OLB-9M*, LB98, MOUB-9, MOT-9, MOLBD-9, MOC-9, MOLB-9	All		45	38	32	24	20	16	14	11	9	8	7	6	3
	OLB-9	All		45	38	32	24	20	16	14	11	9	8	7	3	
	OC-9M*, OLR-9, OLL-9, OT-9M*	All		45	38	32	24	20	16	14	11	9	8	3		
	OC-9, LB97	All		45	38	32	24	20	16	14	11	9	3			
	OT-9, LL97, LR97	All		45	38	32	24	20	16	14	11	3				
	T97, C97	All		45	38	32	24	20	16	3						
3" (-8)	MOUB-8, MOT-8, MOLBD-8, MOC-8, MOLB-8	All		34	28	24	18	15	12	10	8	7	6	5	4	3
	OLB-8, OLR-8, OLL-8, C88, LB888, LL888, LR88	All		34	28	24	18	15	12	10	8	7	6	3		
	OC-8, LL87, LR87, T88	All		34	28	24	18	15	12	10	8	3				
	OT-8M*	All		34	28	24	18	15	12	10	3					
	OT-8, LB87	All		34	28	24	18	15	12	3						
	C87, T87, L87	All		34	28	24	18	15	3							
2-1/2" (-7)	OLB-7	All		22	18	15	11	9	8	6	5	4	4	3		
	OLR-7, OLL-7, C78, LB78, LL78, LR78, MOUB-7, MOT-7, MOLBD-7, MOC-7, MOLB-7	All		22	18	15	11	9	8	6	5	4	3			
	OC-7, LL77, LR77, T78	All		22	18	15	11	9	8	6	5	3				
	OT-7M*	All		22	18	15	11	9	8	6	3					
	OT-7, LB77	All		22	18	15	11	9	8	3						
	C77, T77, L77	All		22	18	15	11	9	3							
2" (-6)	OLR-6, OLL-6	All		15	13	11	8	6	5	4	4	3				
	OLB-6M*, C68, LB68, LL68, LR68, MOUB-6, MOT-6, MOLBD-6, MOC-6	All		15	13	11	8	6	5	4	3					
	T68, TB68, X68	THRU		15	13	11	8	6	5	4	3					
	OC-6M*, OLB-6	All		15	13	11	8	6	5	3						
	T68, TB68, X68	SIDE		15	13	11	8	6	5	3						
	OC-6, OX-6	All		15	13	11	8	6	3							
	OT-6M*, OTB-6M*, C67, LB67, LL67, LR67, T67, TA67, TB67, X67	All		15	13	11	8	3								
	OT-6	All		15	13	11	3									
1-1/2" (-5)	OTB-6	All		15	3											
	OC-5, OLB-5, OLR-5, OLL-5, C58, LB58, LL58, LR58, MOUB-5, MOT-5, MOLBD-5, MOC-5	All		9	8	6	5	3								
	T58, TB58, X58	THRU		9	8	6	5	3								
	C57, LB57, LR57, T57, TA57, TB57, X57	All		9	8	6	3									
	T58, TB58, X58	SIDE		9	8	6	3									
	OT-5, OX-5	All		9	8	3										
1-1/4" (-4)	OTB-5	All	3													
	OC-4, OLB-4, OLR-4, OLL-4, OT-4 OX-4, C47, LB47, LL47, T47, TA47, TB47, X47, C448, LB448, LL448, LR448, T448, TB448, X448, MOUB-4, MOT-4, MOLBD-4, MOC-4	All		6	5	3										
1" (-3)	OTB-4	All	3													
	OC-3, OLB-3, OLR-3, OLL-3, OT-3, OTB-3, OX-3, OE-3, C37, E37, LB37, LL37, LR37, LR37, T37, TA37, TB37, X37, C38, LB38, LL38, LR38, T38, TB38, X38, MOUB-3, MOT-3, MOLBD-3, MOC-3	All		3												
	OTA-3	All	3													
3/4" (-2)	OC-2, OLB-2, OLR-2, OLL-2, OT-2, OTA-2, OTB-2, OX-2, OE-2, C27, E27, LB27, LL27, LR27, T27, TA27, TB27, X27, C28, LB28, LL28, LR28, T28, TB28, X28, MOLBD-2	All	3													