



BG17N

by Burndy
Catalog ID: BG17N

Flexible Copper Braid

Product Details

General

Connector Type	Braid
Material	Copper
UPC	781810550960
UPC 12 Digit	7818105509600

Dimensions

Dimension - D inch	3 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	432 mm
Dimension - Length Overall inch	17 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.50 in

Electrical Ratings

Rating - Indoor Amperage	415 A
Rating - Outdoor Amperage	495 A

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)