


REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	08/29/2018	ADDED HOLE SPACING AND SIZE	49789	JL	BE



NOTES:

- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
- MATERIAL: BRAID - TINNED COPPER
- MATERIAL: FERRULE - TINNED COPPER
- CURRENT CAPACITY: 600 A INDOOR
- BRAID X-SECTION AREA: 308 MCM NOMIAL

TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)

FOR PRODUCT INFO: <http://www.burndy.com>

FLEXIBLE COPPER CONNECTOR

ITEM NO: 50093152

CAT. NO: B4D26W

DRAWN BY: JL BERGERON 7/6/2018

CHECKER: B. ELLIS 7/6/2018

DSN APRVL: H. GOMZ 7/30/2018

MFG APRVL: S. CARABBEAU 7/25/2018

QA APRVL: E. VARGAS 7/18/2018

MKT APRVL: K. ROBICHEAU 7/25/2018

PROD FAM: --

PROJECT #: FPN16011071

DOCUMENT TYPE: SALES

REL LEVEL: Released

BURNDY®

DRAWING NO

CSC.023606-01

SHEET 1 OF 1

REV

B