

GC2929T12



by Burndy
Catalog ID: GC2929T12

Prop 65 Notice

ACCOMMODATES: 2/0 SOL - 250 kcmil Cu BAR SIZE: 1/4" TORQUE: 480 LB-IN SUITABLE FOR DIRECT BURIAL

Product Details

General

Material	Copper Alloy, Cast
Plated	N
Plating Type	Unplated
UPC	781810526415
UPC 12 Digit	7818105264155

Conductor Related

Conductor - Copper Solid Size	#2 AWG - 250 kcmil
-------------------------------	--------------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	200
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)