

Fiber Cleavers

Description	Catalog No.
Multimode fiber only	OFCLV3
SM or MM fiber, precision, with case	① OFCLV5
Replacement blade	OFCLV5RB



①

Microscope, 400X

Includes: built-in illuminator, batteries, SC/ST-style adapter, and soft pouch

Description	Catalog No.
SC/ST-style microscope	② OFSCOPE1
LC adapter (400X microscope only)	FOADPTLC



②

Visual Fault Locators (ST, SC, LC)

Includes: batteries, LC adapter, holster, wrist strap and end protectors

Description	Catalog No.
Visual fault locator	③ OFVFLKT1
LC replacement adapter	④ OFVLCADP



③

TIP: Use a VFL during termination for optimum test results.



④

Microscope, 200X (ST, SC, LC)

Includes: batteries, LC adapter, and soft pouch

Description	Catalog No.
ST, SC, LC microscope	OFSCOPE2



Loose Tube OSP Cable Break-Out Kits

Includes: tube kit, break-out block and crimp bushing

Description	Catalog No.
6-fiber break-out kit	OFBOKT6
12-fiber break-out kit	OFBOKT12



Kevlar® Cable Scissors

Description
For cutting Kevlar reinforced cables up to 24-strand, non-armored

Catalog No.
OFSCSRS



PROclick® Fiber Tool Kit

Description	Catalog No.
Includes:	OFPROKT1
<ul style="list-style-type: none"> Precision cleave tool Strip tool Kevlar scissors Pocket visual fault locator FC-ST OM3 2m launch cord FC adapter insert LC VFL adapter bullet Loose tube anti-slip clamp 	<ul style="list-style-type: none"> Rubber fiber work mat Fiber cleaning fluid Fiber cleaning wipes (90 sheets) Fiber debris collection container Strip tool Safety glasses Carrying case



Note: See PROclick® connectors on page G3 for termination tool applications. Kevlar is a registered trademark of E. I. du Pont de Nemours and Company.