



B2D18N

by Burndy
Catalog ID: B2D18N

Prop 65 Notice

Flexible Copper Braid

Product Details

General

Connector Type	Braid
Material	Copper
UPC	781810164914
UPC 12 Digit	7818101649144

Dimensions

Dimension - D inch	2.50
Dimension - L Length Overall mm	457
Dimension - Length Overall inch	18
Dimension - N inch	0.62
Dimension - Pad Width inch	0.94

Electrical Ratings

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	455

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)