



B2E24

by Burndy
Catalog ID: B2E24

Flexible Copper Braid

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810090930
UPC 12 Digit	7818100909300

Dimensions

Dimension - D inch	3
Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24.00 in
Dimension - N inch	0.75
Dimension - Pad Width inch	1.62

Electrical Ratings

Rating - Indoor Amperage	530
Rating - Outdoor Amperage	635

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467

Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)