

DRAWING NO.
10095473

4

3

2

1

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	05/08/2017 09:32:00 AM	LOGO UPDATE	46694	SV	MB

D

D

C

C


B

B

A

A

REV: PE0200



NOTES:

- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.
- APPROXIMATE AMP RATING: 3,000 A
THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.

TO ORDER BURNDY® PRODUCTS CALL
UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)
CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)
FOR PRODUCT INFO: <http://www.burndy.com>

BRAID			
ITEM NO: 10094157			
CAT. NO: B33G28G20TN			
DRAWN BY: R. BOISVERT 01/13/09			
CHECKER: J. PARKER 01/13/09			
DSN APPVL: J. PARKER 01/05/09			
MFG APPVL: L. LEAVITT 01/05/09			
QA APPVL: J. BRODEUR 01/05/09			
MKT APPVL: P. THERRIEN 01/05/09			
SCALE: 1:2			
PROD FAM: --		DRAWING NO	
PROJECT #: --		10095473	
DOCUMENT TYPE: Sales		B	
REL LEVEL: Released		SHEET 1 OF 1	

BURNDY