


REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	05/31/2018	NEW DRAWING CREATED	49137	YR	VS



NOTES:

- 1 DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
- 2 LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
- 3 LISTED TO CSA 22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS .

TO ORDER BURNDY® PRODUCTS CALL		BRAID, FLEXIBLE	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 50091439	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: B2D14G91TN	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: R.YOGARAJ 5/30/2018	
		CHECKER: S.VENKATESAN 5/29/2018	
		DSN APRVL: S.CARBONNEAU 1/7/2019	
		MFG APRVL: A.SALAZAR 1/7/2019	
		QA APRVL: E.VARGAS 1/7/2019	
		MKT APRVL: K.ROBICHEAU 1/7/2019	DRAWING NO 50091440 REV A
		PROD FAM:	
		PROJECT #: FPN1805082	
		DOCUMENT TYPE: SALES	
		REL LEVEL: Released	
		SIZE B	
		SHEET 1 OF 1	