




DRAWING NO.
10108969

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	5/13/2010 11:10:00 AM	DRAWING RELEASED	21006	RLB	JP



NOTES:

1. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.
2. APPROXIMATE AMP RATING: 1200 INDOOR, 1440 OUTDOOR. THIS MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.

TO ORDER BURNDY® PRODUCTS CALL				BRAID - FLEXIBLE	
UNITED STATES				ITEM NO:	10108536
1-800-346-4175 (LONDONDERRY, NH)				CAT. NO:	B4G72N
CANADA:				DRAWN BY:	M. GOWRISANKAR 11/04/09
1-800-361-6975 (QUEBEC)				CHECKER:	J. PARKER 05/13/10
1-800-387-6487 (ALL OTHER PROVINCES)				DSN APPVL:	J. PARKER 05/06/10
FOR PRODUCT INFO: http://www.burndy.com				MFG APPVL:	-- --
				QA APPVL:	J. BRODEUR 05/10/10
				MKT APPVL:	P. THERRIEN 05/05/10
				PROD FAM:	--
				PROJECT #:	--
				DOCUMENT TYPE:	Sales
				REL LEVEL:	Released
				SIZE	D
				DRAWING NO	10108969
				REV	A
				SCALE: 3:4	SHEET 1 OF 1