



GC2929CG4

by Burndy
Catalog ID: GC2929CG4

Prop 65 Notice

Mechanical Grounding Connector, 2/0 AWG (Sol) -250 kcmil, 1/2"
Stud,Torque:480 lb in.

Product Details

General

Installation Torque Recommended in-lb	480 lb-in
Material	Copper
Plated	N
Plating Type	Unplated
UPC	621945013285
UPC 12 Digit	6219450132855

Dimensions

Dimension - Height inch	2.86 in
Dimension - Length Overall inch	2.04 in
Dimension - Width inch	1.25 in
Dimension - Width mm	32 mm

Conductor Related

Conductor - Copper Solid Size Range	2/0 AWG - 250 KCMIL
-------------------------------------	---------------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)