

YC4A4

by Burndy
Catalog ID: YC4A4

Prop 65 Notice

Al Compression Tap(C-Shaped), 6 Sol. - 4 Str. Al, #6 ACSR(Run), 4 Sol. - 4 Str. Al, #6 ACSR(Tap)



Product Details

General

Die Index	BG
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	CRIMPIT™
Type	YC-A, YC-U Series
UPC	781810122709
UPC 12 Digit	7818101227099

Dimensions

Dimension - Height inch	0.75 in
Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.25 in

Conductor Related

Conductor - AAAC 5005 Tap	30.58 (7) kcmil
Conductor - AAAC 5005 Tap Range	30.58 (7) kcmil
Conductor - AAAC 6201 Tap	30.58 (7) kcmil
Conductor - ACSR Str Run	6
Conductor - ACSR Str Tap	6
Conductor - AL Str Run	6 AWG;4 AWG
Conductor - AL Str Run Range	6 Sol. - 4 Str
Conductor - AL Str Tap Range	4 Sol. - 4 Str.

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)