

DRAWING NO.
10105695

4

3

2

1

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	10/5/2009 3:39:00 PM	DRAWING RELEASED	18945	RLB	JP

D

D

C


C

B

B

A

A



NOTES:

- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.
- APPROXIMATE AMP RATING: 580 A
THIS MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.

REV: PE0200

4

3

2

1

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 10102104	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: B21E12U	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: R. BOISVERT 10/06/09	
		CHECKER: J. PARKER 10/06/09	
		DSN APPVL: J. PARKER 08/21/09	
		MFG APPVL: C. MARTINEZ 09/23/09	
		QA APPVL: J. BRODEUR 09/21/09	
		MKT APPVL: P. THERRIEN 09/21/09	
		SCALE: 1:1	
		PROD FAM: --	DRAWING NO
		PROJECT #: --	10105695
		DOCUMENT TYPE: --	REV
		REL LEVEL: Concept	A