



GXW34C26

by Burndy
Catalog ID: GXW34C26

Prop 65 Notice

Groove A: 450-500 kcmil Cu Groove B: 1/0-2/0 Cu

Product Details

General

Material	Copper Alloy
Plated	N
Plating Type	Unplated
Trade Name	GROUNDWEJ™
UPC	781810428405
UPC 12 Digit	7818104284055

Dimensions

Dimension - B Length inch	1.80 in
Dimension - Pad Width inch	3.30 in

Conductor Related

Conductor - Copper Solid Size B	1/0;2/0
Conductor - Copper Str Size A	450;500
Conductor - Copper Str Size B	1/0;2/0
Conductor - Rod Size	1/2;3/4
Conductor Type	• CU C Str-Size A • CU C Solid-Size A • CU C Str-Size B • CU C Solid-Size B • Rod-Size B

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	16
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)