


REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
B	12/11/07	ADDED FLAGS AND TEXT NOTES 3 & 4		15258	PL DB



NOTES:

1. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
2. APPROXIMATE AMP RATING 380 INDOOR, 455 OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.

3) "UL" SYMBOL PER INTERNAL SPEC. L4219, LOCATION AND SIZE TO BE DETERMINED BY MANUFACTURING.

4) "CSA" SYMBOL PER INTERNAL SPEC. L4591, LOCATION AND SIZE TO BE DETERMINED BY MANUFACTURING.

TO ORDER BURNDY® PRODUCTS CALL 1-800-346-4175
MANCHESTER, NH 03109, USA
FOR PRODUCT INFO = <http://www.fciconnect.com>

BRAID, FLEXIBLE

ITEM NO: 26002039

CAT NO: B2D21G53

SCALE: 1/1	
DRAWN BY: P LAPONIUS	8/4/01
CHECKER: J LETOURNEAU	8/9/01
DSN APPVL: G DITROIA	7/27/01
MFG APPVL: --	--
QC APPVL: S BROWN	7/27/01
MKT APPVL: D HAMILTON	7/27/01
PROD FAM: --	
PROJECT #: --	SIZE
DOCUMENT TYPE: Sales	B
REL LEVEL: AutoCAD	

FCI BURNDY®
PRODUCTS

DRAWING NO: SC213699-01

REV: B

SHEET 1 OF 1