



BD48GTN

by Burndy
Catalog ID: BD48GTN

Tin Plated Copper Braid 48 in Long

Product Details

General

Connector Type	Braid
Material	Copper
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
UPC	621945451858
UPC 12 Digit	6219454518588

Dimensions

Dimension - L Length Overall mm	1219 mm
Dimension - Length Overall inch	48.00 in
Length	48 in
Weight	7.25 lb

Electrical Ratings

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)