

DRAWING NO.
10113779

4

3

2

1

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	6/21/2010 10:27:00 AM	DRAWING RELEASED	21244	RLB	JP

D

D

C

C

B


B

A

A

NOTES:

- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.
- APPROXIMATE AMP RATING: 600 INDOOR, 720 OUTDOOR
THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.



REV: PE0200

TO ORDER BURNDY® PRODUCTS CALL
UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)
CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)
FOR PRODUCT INFO: <http://www.burndy.com>

BRAID			
ITEM NO: 10113729			
CAT. NO: B21F24G5TN			
DRAWN BY: AUGUSTIN		3/01/10	
CHECKER: --		--	
DSN APPVL: --		--	
MFG APPVL: --		--	
QA APPVL: --		--	
MKT APPVL: --		--	
		SCALE: 1:4	
PROD FAM: MECHANICAL GROUNDING		DRAWING NO	REV
PROJECT #: --	SIZE	10113779	A
DOCUMENT TYPE: Sales	C		
REL LEVEL: Released			