



GAR1829TN

by Burndy
Catalog ID: GAR1829TN

Prop 65 Notice

Ground Clamp Copper Tin plated 2/0 AWG-250 Kcmil Installation Torque
Recommended Run in-lb240 LB in

Product Details

General

Installation Torque Recommended Run in-lb	240 Lb-in
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin plated
U Bolt Type	310
UPC	781810079140
UPC 12 Digit	7818100791400

Dimensions

Dimension - B Length inch	2.75 in
Dimension - Height inch	4.50 in
Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.81 in
Dimension - Outside Diameter inch	2.38 in
Dimension - Width inch	3.69 in
Dimension - Width mm	94 mm

Conductor Related

Conductor - Copper Solid Size	2/0 AWG
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	250 Kcmil
Conductor - Copper Str Size Range	1/0-250
Conductor - Copper Tube Std Size	2
Conductor - Copper Tube Std Size Range	2
Conductor - Pipe or Round Tube Size Range	2 in
Conductor - Rod Size	2 in-2.38 in
Conductor - Rod Size Range	2-2 1/4

Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)