



GAR396925BU

by Burndy
Catalog ID: GAR396925BU

Prop 65 Notice

Mechanical Grounding Connector - Conductor to Water Pipe, #8 - 1/0 AWG; 2-1/2" Pipe; UL/CSA; Rated for Direct Burial

Product Details

General

Installation Torque Recommended in-lb	200 lb-in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
UPC	781810421970
UPC 12 Digit	7818104219700

Dimensions

Dimension - Height inch	4.00 in
Dimension - Width inch	4.50 in
Dimension - Width mm	114 mm

Conductor Related

Conductor - Copper Solid Size Range	#8 AWG - 1/0 AWG
Conductor - Copper Str Size	8;7;6;5;4;3;2;1;1/0
Conductor - Copper Str Size Range	8-1/0
Conductor - Copper Tube Std Size	2 1/2
Conductor - Copper Tube Std Size Range	2 1/2
Conductor - Pipe or Round Tube Size	2.50 in

Certifications and Compliance

Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)