

GXW29C58

by Burndy
Catalog ID: GXW29C58

Prop 65 Notice

Accom: Groove A: 4/0 - 250 kcmil Cu Groove B: 4/0 - 250 kcmil Cu 5/8" CuRod



Product Details

General

Material	Copper Alloy
Plated	N
Plating Type	Unplated
Trade Name	GROUNDWEJ™
UPC	781810113295
UPC 12 Digit	7818101132955

Dimensions

Dimension - B Length inch	1.80 in
Dimension - Pad Width inch	2.80 in

Conductor Related

Conductor - Copper Solid Size A	4/0 AWG
Conductor - Copper Solid Size A Range	4/0 AWG
Conductor - Copper Solid Size B	4/0 AWG
Conductor - Copper Solid Size B Range	4/0 AWG
Conductor - Copper Str Size A	4/0 AWG;250 kcmil
Conductor - Copper Str Size A Range	4/0 AWG-250 kcmil
Conductor - Copper Str Size B	4/0 AWG;250 kcmil
Conductor - Copper Str Size B Range	4/0 AWG-250 kcmil
Conductor - Rod Size	5/8;3/4
Conductor - Rod Size B	5/8 in;3/4 in
Conductor - Rod Size B Range	5/8 in-3/4 in
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size A • CU C Solid-Size A • CU C Str-Size B • CU C Solid-Size B • Rod-Size B

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)