


CATALOG NO. 3	ITEM NUMBER	L
BD6G127	25017977	6.00 in
BD12G127	10039700	12.00 in
BD18G127	10068518	18.00 in
BD24G127	10068519	24.00 in

REV.	DATE	DESCRIPTION	ECO	BY	C.H.K.
A	08/11/2011 04:00:00 AM	CREATION OF SALES DRAWING	25309	BD	MA



NOTES:

- APPROXIMATE AMP RATING: INDOOR: 190A, OUTDOOR: 225A. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.
- SUFFIX "TN" DENOTES TIN PLATING.
- ALL SIZES ARE LISTED TO UL 467 GROUNDING AND BONDING EQUIPMENT STANDARDS.
- ALL SIZES ARE LISTED TO CSA C22.2 NO.41 GROUNDING AND BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL  
UNITED STATES:  
1-800-346-4175 (LONDONDERRY, NH)  
CANADA:  
1-800-361-6975 (QUEBEC)  
1-800-387-6487 (ALL OTHER PROVINCES)  
FOR PRODUCT INFO: <http://www.burndy.com>

BRAID			
ITEM NO: (SEE TABLE)			
CAT. NO: BDG127 (SEE TABLE)			
DRAWN BY:	B. DURAICHAMY	08/11/11	<b>BURNDY</b>
CHECKER:	E. MARTIN	08/09/11	
DSN APPVL:	E. MARTIN	08/19/11	
MFG APPVL:	O. GUALBERTO	08/29/11	
QA APPVL:	C. ACKERMAN	08/09/11	
MKT APPVL:	P. THERRIEN	08/09/11	SCALE: 1:1
PROD FAM:	--		
PROJECT #:	--		
DOCUMENT TYPE:	Sales		
REL LEVEL:	Released		
SIZE		DRAWING NO	REV
B		30018577	A
		SHEET 1 OF 1	