



GRC3426

by Burndy
Catalog ID: GRC3426

Prop 65 Notice

ROD: 5/8" & 3/4" WIRE/CABLE MIN.: 8 SOL. WIRE/CABLE MAX.: 2/0 STR.

Product Details

General

Installation Torque Recommended in-lb	170 in-lb
Material	Copper Alloy, Cast
Plated	N
Plating Type	Unplated
UPC	781810424292
UPC 12 Digit	7818104242922

Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	0.65 in

Conductor Related

Conductor - Rod Size	5/8 in , 3/4 in
Conductor Size	#8 AWG - 2/0 AWG
Conductor Type	<ul style="list-style-type: none"> Rod-Size CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)