



ES4R4R

by Burndy Catalog ID: ES4R4R

Prop 65 Notice

RUN/COURSE TAP/DERIVATION ACSR:6 S.B. 200% |6 S.B. 200% AL & CU:4 SOL-4 STR.|4 STR.-4 STR. COLOR/COULEUR: A-ORANGE, B-ORANGE

Product Details

General

Die Index	BG
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
Trade Name	INSULINK™
Туре	Insulated Service Entrance Connectors
UPC	781810420423
UPC 12 Digit	7818104204233

Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

Conductor Related

Conductor - ACSR Str Size A	4 AWG
Conductor - ACSR Str Size B	4 AWG
Conductor - AL Str Size A	4 AWG
Conductor - AL Str Size B	4 AWG
Conductor - Copper Str Size A	4 AWG
Conductor - Copper Str Size B	4 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	СМ

Logistics		
	Minimum Pack Quantity	100

No

For further technical assistance, please contact us

BURNDY Headquarters

UL Listed

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)