




NOTES:

- APPROXIMATE AMP RATING: 600 INDOOR, 720 OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
 - DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- 3 "UL" SYMBOL PER INTERNAL SPEC. L4219, LOCATION AND SIZE TO BE DETERMINED BY MANUFACTURING.

TO ORDER BURNDY®PRODUCTS CALL 1-800-346-4175
MANCHESTER, NH 03109, USA
FOR PRODUCT INFO = <http://www.fciconnect.com>

BRAID, FLEXIBLE

ITEM NO: 10045499

CAT NO: B4D19D75G60TN

SCALE: 1/1		
DRAWN BY: D.BOISVERT 02/04/05		
CHECKER: P.LAPONIUS 02/05/05		
DSN APPVL: J.MICHAUD 10/27/04		
MFG APPVL: N/A ---		
QC APPVL: J.BRODEUR 10/27/04		
MKT APPVL: R.BROOKS 02/02/05		
PROD FAM: ---	DRAWING NO	REV
PROJECT #: ---	10046468	B
DOCUMENT TYPE: Sales	SIZE	
REL LEVEL: AutoCAD	D	
SHEET 1 OF 1		