



BE60G169TN

by Burndy
Catalog ID: BE60G169TN

Tin Plated Ferrules

Product Details

General

Connector Type	Braid
Material	Copper
UPC	781810512005
UPC 12 Digit	7818105120055

Dimensions

Dimension - L Length Overall mm	1524 mm
Dimension - Length Overall inch	60 in

Electrical Ratings

Rating - Indoor Amperage	340 A
Rating - Outdoor Amperage	405 A

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)