

CT50300M00

by Burndy
Catalog ID: CT50300M00

Nylon UNIRAP - 50 Lb. Tensile Strength

- Standard Cable Tie



Product Details

General

| | |
|---------------------------------------|---------------|
| Color | Black |
| Color Code | Black |
| Material | Nylon 6/6 |
| Military Specification | MS3367 |
| Operating Temperature Celcius Max | 85 °C |
| Operating Temperature Celcius Min | -40 °C |
| Rating - Minimum Tensile Strength N | 50 |
| Rating - Minimum Tensile Strength lbs | 50 |
| Trade Name | UNIRAP™ |
| UPC | 781810332832 |
| UPC 12 Digit | 7818103328322 |

Dimensions

| | |
|--------------------------------------|---------|
| Dimension - Bundle Diameter Max inch | 3 |
| Dimension - L Length Overall mm | 282 mm |
| Dimension - Length Overall inch | 11.1 in |
| Dimension - Width fraction | 9/50 in |
| Dimension - Width inch | 0.18 in |
| Dimension - Width mm | 5 mm |

Certifications and Compliance

| | |
|------------------------------------|-------------------------------|
| Certification - 94V0 Rated | N |
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - UV Rated | Yes |
| Certification - cULus | Yes |
| Industry Standard(s) | Military Specified (Mil-Spec) |
| Military Spec Number | MS3367-7-0 |
| Standards - Industry Standards Met | Military Specified (Mil-Spec) |
| Standards - RoHS Compliance Status | CM |

| | |
|-----------|----|
| UL Listed | No |
|-----------|----|

Logistics

| | |
|-----------------------|---------|
| Carton Quantity | 5000 EA |
| Minimum Pack Quantity | 5000 |
| Packaging Type | Bag |

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)