



REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	12/14/2017	NEW DRAWING CREATED	48135	PB	RG



NOTES:

- 1. MATERIAL: CAST COPPER ALLOY.
- 2. ACCOMMODATES: 2/0 SOL. (.365 DIA.) TO 250 kcmil (.575 DIA.).
- 3. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com		GROUND CLAMP	
		ITEM NO: 27018671 CAT. NO: GBM29CG14 DRAWN BY: B.PARTHIBAN 12/14/2017 CHECKER: E.MARTIN 1/10/2018 DSN APRVL: E.MARTIN 1/10/2018 MFG APRVL: T.WAWRZYNIAK 1/11/2018 QA APRVL: J.HILLMAN 1/11/2018 MKT APRVL: -- PROD FAM: -- PROJECT #: -- DOCUMENT TYPE: SALES REL LEVEL: Released	
		DRAWING NO 50088195 SHEET 1 OF 1	REV A