

DRAWING NO.
10099271




4

3

2

1

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	3/24/2009 12:00:00 AM	CREATE PRODUCTION AND SALES DRAWINGS FOR BRAID B2E1075G1	17758	DG	MA



3D-VIEW

NOTES:

1. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.
2. APPROXIMATE AMP RATING: 530 INDOOR, 635 OUTDOOR
THIS MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.

TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)

FOR PRODUCT INFO: <http://www.burndy.com>

BRAID, FLEXIBLE

ITEM NO: 10094258

CAT. NO: B2E1075G1

DRAWN BY: D.GANESH 03/24/2009

CHECKER: J.PARKER 04/08/2009

DSN APPVL: J.PARKER 04/08/2009

MFG APPVL: L.LEAVITT 03/30/2009

QA APPVL: J.BRODEUR 03/31/2009

MKT APPVL: P.THERRIEN 03/27/2009

PROD FAM: --

PROJECT #: --

DOCUMENT TYPE: Sales

REL LEVEL: Released



SCALE: 3:4

DRAWING NO

10099271

SHEET 1 OF 1

REV

A

REV: PE0200

4

3

2

1