



REV.	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	04/07/03	MADE CHANGES PER ECO	8319	BJM	RLB

### ACCESSORIES

LEATHER HOLDER  
CATALOG NUMBER, PT4583

- \* TOP GRAIN COWHIDE SADDLE LEATHER.
- \* LARGE GROMMET.

NO-GO GAUGE  
CATALOG NUMBER, PT8504

GAUGE IS USED TO CHECK THE OH25 HYTOOL CRIMP DIMENSIONS.

### ACCOMMODATES:

- \* 5/8 SERVICE ENTRANCE SLEEVES.
- \* INSULINK™ TYPE ES (INSULATED) #10 - 1/0 STR
- \* LINKIT™ TYPE YSU (BARE) #8 - 1/0 STR.
- \* 5/8 NEUTRAL TENSION SLEEVES HYSPLICE™ TYPES YSS, YCS-R, YDS-AT #4 - 1/0.
- \* AYP HYPLUG™ #6 - 1/0 STR.

### SELECTED APPLICATIONS

CONDUCTOR RANGE: #10 THROUGH 1/0

### NOTE:

- DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER AND ARE FOR REFERENCE ONLY.

### OH25 HYTOOL™

#### SPECIFICATIONS:

MAXIMUM FORCE DEVELOPED - 6000 LBS.  
MAXIMUM FORCE ON HANDLES - 50 LBS.  
WEIGHT: 2 LBS. 11 OZ.

#### JAWS:

HIGH STRENGTH STEEL, AND REPLACEABLE POLISHED STEEL INDENTOR.

#### HANDLES:

SPRING LOADED, ONE PIECE STEEL WITH COMFORT GRIP DESIGN AND ERGONOMIC HANDLE ENDS PROVIDES A POSITIVE, ANTI-SLIP GRIP

#### TYPE OF MECHANISM:

HAND DRIVEN FULL CYCLE RATCHET/CAM AND TOGGLE WITH CAM COMPENSATOR. FIRST FEW STROKES GRIP CONNECTOR. POSITIVE RATCHET HOLDS CONNECTOR UNTIL CRIMP IS COMPLETE.

"MINI-CLICK" MODE PROVIDES EASIER OPERATION WHEN HIGH HAND FORCE IS NEEDED.

PROPER CRIMPS ARE MADE WITH FULL CYCLE RATCHET MECHANISM.

TO ORDER BURNDY PRODUCTS CALL 1-800-346-4175  
MANCHESTER, NH 03109, USA  
FOR PRODUCT INFO = <http://www.burndy.com>

### HYTOOL™, ONE HAND TOOL

ITEM NO: 468200

CAT NO: OH25

SCALE:	0.500
DRAWN BY:	-- 01/01/01
CHECKER:	-- 01/01/01
DSN APPVL:	J AYER 01/01/01
MFG APPVL:	S GONYAW 01/01/01
QA APPVL:	J BRODEUR 01/01/01
MKT APPVL:	R POIRIER 01/01/01



PROD FAM:	MECH TOOLS	DRAWING NO	REV
PROJECT#	--	SIZE	B
DOCUMENT TYPE:	--	SC210780-01	B
REL LEVEL:	Released	SHEET 1 OF 1	