



GL3434T8

by Burndy
Catalog ID: GL3434T8

Prop 65 Notice

ACCOM: 300-500kcmil CU BAR SIZE: 1/2" - 1"

Product Details

General

Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
UPC	781810042809
UPC 12 Digit	7818100428099

Dimensions

Dimension - B Length inch	2.81 in
Dimension - D inch	2.56 in
Dimension - F Width Center to Center inch	1.38 in
Dimension - Length Side B inch	2.50 in
Dimension - Pad Width inch	1.44 in
Dimension - Width fraction	2-7/8 in
Dimension - Width inch	2.88 in
Dimension - Width mm	73 mm

Conductor Related

Conductor - Copper Str Size	300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	300 kcmil-500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

UL Listed	Yes
-----------	-----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)