



GG151SE

by Burndy
Catalog ID: GG151SE

Prop 65 Notice

Cast Cu Alloy Ground Connector, 1" IPS, 1-1/8" - 1-1/4" Rod, 3/8" Bolt

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	244
UPC	781810042762
UPC 12 Digit	7818100427622

Dimensions

Dimension - B Length inch	1.31 in
Dimension - Braid Width Max fraction	1 in
Dimension - Braid Width Max inch	1.00 in
Dimension - Height inch	3.38 in
Dimension - Width fraction	2-5/8 in
Dimension - Width inch	2.63 in
Dimension - Width mm	67 mm

Conductor Related

Conductor - Copper Str Size B Range	1
Conductor - Copper Tube Std Size	1-1/8;1-1/4
Conductor - Copper Tube Std Size Range	1-1/8-1-1/4
Conductor Type	- Rod-Size - CU Tube Std-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)