


REV.	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	4/18/2011 12:00:00 AM	FOCUS REQUEST	24137	BD	JG



NOTES:

- DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- APPROXIMATE AMP RATING: 93A. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.

TO ORDER BURNDY® PRODUCTS CALL  
 UNITED STATES:  
 1-800-346-4175 (LONDONDERRY, NH)  
 CANADA:  
 1-800-361-6975 (QUEBEC)  
 1-800-387-6487 (ALL OTHER PROVINCES)  
 FOR PRODUCT INFO: <http://www.burndy.com>

BRAID			
ITEM NO: 30014135			
CAT. NO: BB024L5D90G54TN			
DRAWN BY: M. AYYAPPAN	04/04/11	<b>BURNDY</b>	
CHECKER: E. MARTIN	05/04/11		
DSN APPVL: E. MARTIN	05/04/11		
MFG APPVL: O. GUALBERTO	05/05/11		
QA APPVL: C. ACKERMAN	05/05/11		
MKT APPVL: --	--	SCALE: 3:2	
PROD FAM: MECHANICAL GROUNDING	DRAWING NO	REV	
PROJECT #: --	SIZE	30014136	
DOCUMENT TYPE: Sales	B	SHEET 1 OF 1	
REL LEVEL: Released		A	