



ES6R6R

by Burndy
Catalog ID: ES6R6R

Prop 65 Notice

RUN/COURSE TAP/DERIVATION ACSR:6(6-1),6 S.B.100%|8 S.B. 100/150%
AL & CU: 6 SOL-6 STR. |6 SOL-6 STR. COLOR/COULEUR: A-BLUE, B-BLUE

Product Details

General

Die Index	BG
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
Trade Name	INSULINK™
Type	Insulated Service Entrance Connectors
UPC	781810420393
UPC 12 Digit	7818104203933

Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in
Length	2.78 in

Conductor Related

Conductor - ACSR Str Size A	6 AWG
Conductor - ACSR Str Size B	6 AWG
Conductor - AL Str Size A	6 AWG
Conductor - AL Str Size B	6 AWG
Conductor - Copper Str Size A	6 AWG
Conductor - Copper Str Size B	6 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)