



## GAR2134

by Burndy  
Catalog ID: GAR2134

Prop 65 Notice

Mechanical Grounding Connector, Cable to Rod or Pipe, 300 kcmil -500 kcmil, 3-1/2" Pipe, 3-1/2"-4" Rod, Bright Dipped

## Product Details

### General

Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Bright Dipped
U Bolt Type	436
UPC	781810237052
UPC 12 Digit	7818102370522

### Dimensions

Dimension - B Length inch	4.25 in
Dimension - Height fraction	6-3/4 in
Dimension - Height inch	6.75 in
Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.38 in
Dimension - Outside Diameter inch	4.00 in
Dimension - Width fraction	5-3/4 in
Dimension - Width inch	5.69 in
Dimension - Width mm	145 mm

### Conductor Related

Conductor - Copper Solid Size Range	300 Kcmil -500 Kcmil
Conductor - Copper Str Size	300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	300 kcmil-500 kcmil
Conductor - Copper Tube Std Size	3 1/2 IPS IPS
Conductor - Copper Tube Std Size Range	3 1/2 IPS IPS
Conductor - Pipe or Round Tube Size	3 1/2 in
Conductor - Rod Size	3.5 - 4.0 in
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> <li>• CU Tube Std-Size</li> <li>• Rod-Size</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	4
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)