


ITEM NO.	CATALOG NO.	LENGTH (L)
10094104	B2ID12G3TN	12 [305]
10094105	B2ID18G3TN	18 [457]
10094106	B2ID42G3TN	42 [1067]

REV.	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	6/6/2011 12:00:00 AM	NEW DRAWING RELEASE	24698	AD	MA



- NOTES:
1. APPROXIMATE AMP RATING: 380A. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
 2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
 3. SUFFIX "TN" DENOTES TIN PLATING.

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com		BRAID	
		ITEM NO: SEE TABLE	
		CAT. NO: B2ID--G3TN (SEE TABLE)	
		DRAWN BY: S.AUGUSTIN 06/06/11	
		CHECKER: E.MARTIN 06/03/11	
		DSN APPVL: E.MARTIN 06/03/11	
		MFG APPVL: O.GUALBERTO 06/14/11	
		QA APPVL: C.ACKERMAN 06/08/11	
		MKT APPVL: P.THERRIEN 06/03/11	
		PROD FAM: MECHANICAL GROUNDING	SCALE: 3:4
		PROJECT #: --	DRAWING NO
		DOCUMENT TYPE: Sales	REV
		REL LEVEL: Released	SIZE
		B	30016518
			SHEET 1 OF 1
			A