

DRAWING NO.
10092244

4

3

2

1

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	9/16/2008 4:11:00 PM	DRAWING RELEASED	16683	RLB	JP

D

D

C


C

B

B

A

A



NOTES:

- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.
- APPROXIMATE AMP RATING: 340 INDOOR, 405 OUTDOOR
THIS MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
- ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
- ALL SIZES ARE LISTED TO CSA 22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.fciconnect.com		BRAID	
		ITEM NO: 33216F	CAT. NO: BE24G114
FCI		DRAWN BY: R. BOISVERT 09/17/08	CHECKER: J. PARKER 09/17/08
		DSN APPVL: J. PARKER 09/02/08	MFG APPVL: L. LEAVITT 09/11/08
QA APPVL: J. BRODEUR 09/15/08		MKT APPVL: P. THERRIEN 09/11/08	SCALE: 3:4
		PROD FAM: --	DRAWING NO: 10092244
PROJECT #: --		SIZE: C	REV: A
		DOCUMENT TYPE: --	SHEET 1 OF 1
REL LEVEL: Released			

4

3

2

1

REV: PE0200