

by Burndy  
Catalog ID: ES8R8R

RUN/COURSE TAP/DERIVATION ACSR:8 S.B. 100/150 % | 8 S.B. 100/150 %  
AL & CU: 8 SOL.-8 STR.| 8 SOL.-8 STR COLOR/COULEUR: A-GREEN, B-  
GREEN

## General

Die Index	BG
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
Trade Name	INSULINK™
Type	Insulated Service Entrance Connectors
UPC	781810420362
UPC 12 Digit	7818104203622

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Minimum Pack Quantity	100
-----------------------	-----

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)