



CT30125C00

by Burndy
Catalog ID: CT30125C00

Nylon cable ties, Tensile strength-250 Lbs, Color- UV Black, 05.84"L,
0.14"W, 01.25" Bundle Dia.

- Standard Cable Tie

Product Details

General

Color	UV Black (Mil. Spec.)
Material	Nylon 6/6
Military Specification	MS3367
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	30
Tool Type	Intermediate
Trade Name	UNIRAP™
UPC	781810332283

Dimensions

Dimension - Bundle Diameter Max inch	1.25 in
Dimension - L Length Overall mm	146 mm
Dimension - Length Overall inch	5.75 in
Dimension - Width inch	0.14 in
Dimension - Width mm	3.6 mm

Certifications and Compliance

Certification - 94VO Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-5-0
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000 EA
-----------------	---------

Minimum Pack Quantity	100
Packaging Type	Bag

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)