


| CATALOG<br>NUMBER | LENGTH<br>"L" |
|-------------------|---------------|
| B24G184N          | 18<br>[457]   |
| B24G244N          | 24<br>[610]   |
| B24G364N          | 36<br>[914]   |

| REV | DATE       | DESCRIPTION         | ECO   | BY | C'H'K. |
|-----|------------|---------------------|-------|----|--------|
| A   | 02/26/2019 | NEW DRAWING CREATED | 50891 | PB | RG     |



NOTES:

1. MATERIAL : FERRULES - COPPER  
BRAID - TINNED COPPER
2. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
3. CAN BE ORDERED WITH PLATED FERRULES BY ADDING SUFFIX AS SHOWN BELOW:  
"NK" - FOR NICKEL PLATING  
"SV" - FOR SILVER PLATING  
"TN" - FOR TIN PLATING  
"W" - FOR HOT TIN PLATING
4. CAN BE ORDERED WITH UNDRILLED FERRULES BY ADDING SUFFIX "U".

TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES  
1-800-346-4175 (LONDONDERRY, NH)

CANADA:  
1-800-361-6975 (QUEBEC)  
1-800-387-6487 (ALL OTHER PROVINCES)

FOR PRODUCT INFO: <http://www.burndy.com>

|                                |  |              |     |
|--------------------------------|--|--------------|-----|
| BRAID                          |  |              |     |
| ITEM NO: --                    |  |              |     |
| CAT. NO: B24G--4N(SEE TABLE)   |  |              |     |
| DRAWN BY: B.PARTHIBAN          |  | 02/26/2019   |     |
| CHECKER: S.CARBONNEAU          |  | 04/24/2019   |     |
| DSN APRVL: S.CARBONNEAU        |  | 04/24/2019   |     |
| MFG APRVL: P.MARTEL            |  | 04/23/2019   |     |
| QA APRVL: C.LINDOUST           |  | 04/25/2019   |     |
| MKT APRVL: K.ROBICHEAU         |  | 04/25/2019   |     |
| PROD FAM: MECHANICAL GROUNDING |  | DRAWING NO   | REV |
| PROJECT #: --                  |  | 50099446     | A   |
| SIZE                           |  |              |     |
| DOCUMENT TYPE: SALES           |  |              |     |
| REL LEVEL: Released            |  | SHEET 1 OF 1 |     |