

DRAWING NO.
10102048

4

3

2

1

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	9/9/2009 3:23:00 PM	DRAWING RELEASED	18969	RLB	JM

D

D

C

C

B

B




A

A

REV: PE0200

NOTES:

1. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.
2. APPROXIMATE AMP RATING: 470 INDOOR, 560 OUTDOOR
THIS MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.



TO ORDER BURNDY® PRODUCTS CALL
UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)
CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)
FOR PRODUCT INFO: <http://www.burndy.com>

BRAID			
ITEM NO: 10102047			
CAT. NO: B3D7G65			
DRAWN BY:	R. BOISVERT	09/09/09	BURNDY
CHECKER:	J. MICHAUD	09/10/09	
DSN APPVL:	J. MICHAUD	08/26/09	
MFG APPVL:	C. MARTINEZ	09/02/09	
QA APPVL:	J. BRODEUR	09/01/09	
MKT APPVL:	P. THERRIEN	08/25/09	SCALE: 1:1
PROD FAM:	--	DRAWING NO	REV
PROJECT #:	--	10102048	A
DOCUMENT TYPE:	--	SHEET 1 OF 1	
REL LEVEL:	Released		