



GRL3

by Burndy
Catalog ID: GRL3

Prop 65 Notice

Light Duty; #10-#4 AWG Copper; 3/8"; Direct Burial

Product Details

General

Material	Copper Alloy
Plated	N
Plating Type	Unplated
UPC	781810051801

Conductor Related

Conductor - Copper Str Size Range	10 AWG-4 AWG
Conductor - Rod Size	3/8 in
Conductor Size	#4 AWG - #10 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)