



GD2129W

by Burndy
Catalog ID: GD2129W

Prop 65 Notice

IPS: 3 - 1/2" ROD: 3 - 1/2 - 4" CABLE: 2/0 SOL. - 250 KCMIL

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin - Hot Dipped
U Bolt Type	264
UPC	781810079157
UPC 12 Digit	7818100791577

Dimensions

Dimension - B Length inch	1.50 in
Dimension - Width fraction	5-1/3 in
Dimension - Width inch	5.31 in
Dimension - Width mm	135 mm

Conductor Related

Conductor - Copper Solid Size	2/0;3/0;4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	2/0;3/0;4/0;250
Conductor - Copper Str Size B Range	3.5
Conductor - Copper Str Size Range	2/0-250
Conductor - Copper Tube Std Size	3-1/2
Conductor - Copper Tube Std Size Range	3-1/2

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467

Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)