


CAT.NO	LENGTH
B2F52G141	52"
B2F48G141	48"
B2F44G141	44"
B2F40G141	40"

REV	DATE	DESCRIPTION	ECO	BY	CH'K.
A	11/02/2012	SALES DRAWING REDRAW IN INVENTOR	29295	YM	MB



NOTES:

1. MATERIALS :
BRAID - TIN - PLATED COPPER
FERRULES - COPPER
2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
3. APPROXIMATE AMP RATING: 600 A INDOOR, 720 A OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.

4 ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY PRODUCTS CALL		BRAID	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: N/A	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: B2F-G141(SEE TABLE)	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: PW 7/10/2001	
		CHECKER: TORRES 7/9/2001	
		DSN APRVL: --	
		MFG APRVL: --	
		QA APRVL: --	
		MKT APRVL: --	
		PROD FAMI: --	
		PROJECT #: SALES	
		REL LEVEL: Released	
		SIZE B	
		DRAWING NO 50014635	
		REV A	
		SHEET 1 OF 1	