

# CT50175C00

by Burndy  
Catalog ID: CT50175C00

Nylon cable ties, Tensile strength-50 Lbs, Color- UV Black, 07.56"L,  
0.18"W, 01.87" Bundle Dia.

- Standard Cable Tie



## Product Details

### General

Color	UV Black (Mil. Spec.)
Material	Nylon 6/6
Military Specification	MS3367
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	50
Tool Type	Standard
Trade Name	UNIRAP™
UPC	781810332801

### Dimensions

Dimension - Bundle Diameter Max inch	1.87 in
Dimension - L Length Overall mm	192 mm
Dimension - Length Overall inch	7.56 in
Dimension - Width inch	0.18 in
Dimension - Width mm	5 mm

### Certifications and Compliance

Certification - 94VO Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-1-0
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	10000 EA
-----------------	----------

Minimum Pack Quantity	100
Packaging Type	Bag

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)