

DRAWING NO.
30023134

4

3

2

1

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	01/05/2012 00:00:00 AM	CREATE PRODUCTION DRAWING FOR BE36G183TN	26433	TM	MA

D

D

C

C

B

B

A


A

REV: PE0200

NOTES:

1. APPROXIMATE AMP RATING: 340A INDOOR, 405A OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

- 3 ALL SIZE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
- 4 ALL SIZE LISTED TO CSA 22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.



TO ORDER BURNDY® PRODUCTS CALL UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com	BRAID			
	ITEM NO: 30023133			
	CAT. NO: BE36G183TN			
	DRAWN BY: E.MARTIN		12/13/2011	
	CHECKER: E.MARTIN		12/28/2011	
	DSN APPVL: E.MARTIN		12/28/2011	
	MFG APPVL: --		--	
	QA APPVL: A.PINEDA		01/19/2012	
	MKT APPVL: P.THERRIEN		01/06/2012	
	SCALE: 3:4			
PROD FAM: Mechanical Grounding		DRAWING NO	REV	
PROJECT #: --		SIZE	30023134	
DOCUMENT TYPE: Sales		C	A	
REL LEVEL: Released		SHEET 1 OF 1		