



## GD2029W

by Burndy  
Catalog ID: GD2029W

Prop 65 Notice

IPS: 3" ROD: 3 - 3 1/2" CABLE: 2/0 SOL. - 250 KCMIL

## Product Details

### General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin - Hot Dipped
U Bolt Type	258
UPC	781810247815
UPC 12 Digit	7818102478155

### Dimensions

Dimension - B Length inch	1.50 in
Dimension - Width fraction	4-4/5 in
Dimension - Width inch	4.81 in
Dimension - Width mm	122 mm

### Conductor Related

Conductor - Copper Solid Size	2/0;3/0;4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	2/0;3/0;4/0;250
Conductor - Copper Str Size B Range	3
Conductor - Copper Str Size Range	2/0-250
Conductor - Copper Tube Std Size	3
Conductor - Copper Tube Std Size Range	3

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467

Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)