

DRAWING NO.
30020502

4

3

2

1

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	12/20/2011 21:00:00 PM	DRAWING RELEASED FOR PRODUCTION	26388	RG	MA

D

D

C



C

B

B

A

A



NOTES:

- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- APPROXIMATE AMP. RATING: 180A, THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
- LISTED TO UL 467 GROUNDING AND BONDING EQUIPMENT STANDARDS.
- LISTED TO CSA C22.2 NO. 41 GROUNDING AND BONDING EQUIPMENT STANDARDS.

REV: PE0200

4

3

2

1

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com	BRAID			
	ITEM NO: 30017890			
	CAT. NO: BB067L32G16TN			
	DRAWN BY: N.D.KANNAN		10/04/11	
	CHECKER: E.MARTIN		12/19/11	
	DSN APPVL: E.MARTIN		12/19/11	
	MFG APPVL: --		--	
	QA APPVL: A.PINEDA		01/30/12	
	MKT APPVL: P.THERRIEN		12/19/11	
			SCALE: 1:1	
PROD FAM: Mechanical Grounding		DRAWING NO	REV	
PROJECT #: --		30020502	A	
DOCUMENT TYPE: Sales		SHEET 1 OF 1		
REL LEVEL: Released				