



REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	05/05/2017 08:13:00 AM	LOGO UPDATED --	46682	SM	MB



- NOTES:
- DIMENSION IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
 - MATERIAL: BRAID- TINNED COPPER.
FERRULES- TINNED COPPER.
 - APPROXIMATE AMP. RATING: INDOOR 415A OUTDOOR: 495A
THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.

TO ORDER BURNDY® PRODUCTS CALL
UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)
CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)
FOR PRODUCT INFO: <http://www.burndy.com>

COPPER BRAID FLEXIBLE CONNECTOR

ITEM NO: 10099386

CAT. NO: BG12G109TN

DRAWN BY: S. PANDIAN	05/04/09
CHECKER: J. PARKER	06/30/09
DSN APPVL: J. PARKER	06/24/09
MFG APPVL: --	--
QA APPVL: J. BRODEUR	06/25/09
MKT APPVL: P. THERRIEN	06/24/09
PROD FAM: --	--
PROJECT #: --	SIZE
DOCUMENT TYPE: Sales	C
REL LEVEL: Released	--

SCALE: 7:8

DRAWING NO
10101266

REV
B

SHEET 1 OF 1

REV: PE0200