


NOTES:

- APPROXIMATE AMP RATING: 1,500 A.
THIS RATING MAY VARY WITH AMBIENT CONDITIONS,
ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE
NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY®PRODUCTS CALL 1-800-346-4175
MANCHESTER, NH 03109, USA
FOR PRODUCT INFO = <http://www.fciconnect.com>

BRAID

ITEM NO: 10039507

CAT NO: B32F18D13G14

SCALE: 1/1		
DRAWN BY: D.BOISVERT 04/07/04		
CHECKER: -- --		
DSN APPVL: J.MICHAUD 04/01/04		
MFG APPVL: N/A --		
QC APPVL: J.BRODEUR 04/01/04	DRAWING NO	REV
MKT APPVL: R.BROOKS 04/01/04		
PROD FAM: --	10040062	A
PROJECT #: --		
DOCUMENT TYPE: Sales	SIZE	SHEET 1 OF 1
REL LEVEL: AutoCAD	D	