



GB26T4TN

by Burndy
Catalog ID: GB26T4TN

Mechanical Grounding Connector, Cable to 1/2" Thick Bar, 4 AWG
(Sol)-2/0 AWG (Str), Tin Plated

Product Details

General

Installation Torque Recommended in-lb	240 lb-in
Plated	N
Plating Type	Tin Plated
UPC	781810541135
UPC 12 Digit	7818105411355

Dimensions

Dimension - B Length inch	1.06 in
Dimension - Height inch	2.18 in
Dimension - Length Overall inch	0.94 in
Dimension - Width fraction	1-5/9 in
Dimension - Width inch	1.56 in

Conductor Related

Conductor - Copper Solid Size Range	4 AWG-2/0 AWG
-------------------------------------	---------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)